# FEP ME 975 HC





## FEP ME 975 HC

FEP ME 975 HC is a compact x-ray inspection system, ideal for screening of hold baggage and small or mid-sizeed items.

FEP ME 975 HC features the most advanced detection technology, acquisition electronics, and PC data management software.

The control console is ergonomically designed for faster screening.

- Real time image processing at 24-bit
- Resolution and penetration at highest levels
- Visualization of black & white and color images on switchable single monitor, or on optional double monitor system
- Implementation of key enhancements "on
- Innovative new digital archiving system
- Ability to automatically store working sessions

#### **TECHNICAL SPECIFICATIONS**

#### Inspection unit

- •Dimensions:
- 2980mm (L) x 1225mm (W) x 1737mm (H)
- Weight: 650kg
- Maximum bag dimension: 900mm (W) x 750mm (H)
- Conveyor belt height: 780mm (adjustable)
- Conveyor belt speed: 0.2m/s
- Maximum load: 200kg
- Power supply:
  - monophase, 230 Vac or 110 Vac +/- 10%
- Frequency: 50/60Hz +/- 3Hz
- Power absorbed: < 1.5kVA
- Duty cycle: 100%

### Control unit

- Operator workstation dimensions: 900mm (L) x 800mm (W) x 750mm (H)
- Weight: 30kg
- Controls:

Key switch

Belt start button

Processing buttons

Zoom buttons

Alarm button

Emergency Stop

• Monitor: 17" SVGA, 1024 x 768

#### X-Ray generator

• High frequency monoblock: 30kHz

• X-ray tube voltage: 145kV

• X-ray tube current: 1mA



Black & white image: High-quality image for recognition of threat objects (gun, knives, etc.)



Color image: Materials are represented as orange for organic, blue for metal, green for inorganic (other than metal)



Optional ADS software (red outline)

#### Detection system features

• Resolution:

36 AWG guaranteed 38 AWG typical

• Penetration:

26mm steel guaranteed 28mm steel typical

• Detectors:

1152 photodiodes on two rows, "L" shape

#### Standard image enhancement features

- Material separation
- Contrast optimization
- Edge enhancement
- Reverse image
- "Low color levels" removal
- Energy stripping
- Hystogram equalization
- Pseudo colours
- Zoom x 2 ... x 64
- All features available "on the fly"

#### Advanced functions

- Density alarm (adjustable threshold)
- Organic alarm (adjustable threshold)
- ADS (optional)
- TIP (optional)
- Network TIP (optional)
- Digital image storage
- Automatic worksession archiving, with off-line post-processing

#### X-Ray protection information


- The system complies with applicable international regulations on X-Ray protection
- Leakage dose at 10cm:<1.0µSv/h (0.1mR/h)
- Film safety: guaranteed up to ISO 1600/33 DIN

#### Environmental compliance

- Operational temperatures: 0°C 40°C
- Storage temperature: -20°C +60°C
- Humidity: 90% non condensing
- Protection class: IP22
- Noise level: < 60dB (A)



## FEP ME 975 HC



Dimensions in mm

Reserving the right to improve and modify

RESEARCH LABORATORIES acknowledged "Highly Qualified" with decree D.M. 9-10-1985 – L.46/82 art.4

Head office and facilities: Via Arturo Gilardoni, 1 - 23826 Mandello del Lario (LC) - Italy

tel. (+39) 0341-705.111 - fax (+39) 0341-735.046 e-mail: security@gilardoni.it - www.gilardoni.it

Export department: tel. (+39) 0341-705.224 - 0341-705.281

REFERENCE RULES: EC, IEC, FAA, ICRP, CE marking







